



Technical resources

Screening Ball Mill

Model: MS

<https://www.tencanballmills.com/en/products/grinding-series/drum-ball-mill/screening-ball-mill.html>

09.10.2026 / TENCAN

Screening Ball Mill

Model: MS

Screening ball mill integrates grinding and sieving in one unit. Material is continuously fed, ground, and sieved to target particle size. Ideal for powder processing industries.

Technical specifications

Loading capacity	10~66L
Variable frequency speed	10~72r/min
Equipment weight	290~445kg

These specifications describe the series. Confirm the selected model, power supply and configuration before ordering.



Screening mill (screening mill) It consists of a ball mill drum, a screen system, a feeding system, and a collecting system. The material can be crushed and screened during the ball milling process. After the material reaches the particle size, it is screened out by the screen system. The screened out material is collected by the collecting system, and the material is continuously fed through the feeding system. For materials, the grinding and screening machine is particularly suitable for materials that need to be crushed to a specific particle size. For example, if you want to obtain a specific range, such as 200-300 mesh materials, the grinding and screening machine is very suitable. In addition, the grinding and screening machine also greatly improves the grinding efficiency and reduces unnecessary repeated ball milling.

Screening mill (screening mill) Generally, it is customized according to the customer's requirements, and the customer provides the crushing particle size range, crushing bin volume, and crushing bin material required by the grinding and screening machine.



Technical parameters

model	Frequency conversion speed (r/min) ± 3	Motor (kw)	Motor series	Voltage	Loading capacity L	The discharge port is off the ground	Equipment weight	Mill barrel size	Overall dimensions (reference dimensions) mm
MS-30	10-72	1.5	4	Single phase 220V	10	480mm	About 290kg	$\Phi 320 \times 420 \times 5$ mm	1690x650x1360
MS-60	10-68	2.2		Three-phase 380V	20	580mm	About 350kg	$\Phi 382 \times 580 \times 6$ mm	1856x700x1500
MS-100	10-58	3		Three-phase 380V	33	530mm	About 445kg	$\Phi 455 \times 610 \times 8$ mm	1910x700x1500
MS-200	10-58	5.5		380V	66	~	~	~	About 2200x820x1600

Screening mill (screening mill) When working, the grinding media and materials in the cylinder are raised to a certain height with the rotation of the cylinder. Due to the action of gravity, they break away from the cylinder wall and fall along a parabola. The materials are crushed under the impact of the grinding media and the friction and shear caused by the rolling and sliding of the grinding media. Grinding and screening machines can be widely used in electronic materials, magnetic

materials, biomedicine, ceramic glaze slurry, non-metallic minerals, new materials and other industries.

Contact

Changsha Tianchuang Powder Technology Co., Ltd. / Changsha, Hunan, China

Email: lichang0516@gmail.com

Phone / WhatsApp: +86 731 84027560 / WhatsApp +86 19021571516

<https://www.tencanballmills.com/en/products/grinding-series/drum-ball-mill/screening-ball-mill.html>

Before operation, review the selected model's instructions and the material requirements.