



Technical resources

Liquid Nitrogen Planetary Ball Mill

Model: XQM

<https://www.tencanballmills.com/en/products/grinding-series/planetary-ball-mill/liquid-nitrogen-planetary-ball-mill.html>

09.10.2026 / TENCAN

Liquid Nitrogen Planetary Ball Mill

Model: XQM

Cryogenic planetary ball mill with liquid nitrogen cooling for heat-sensitive materials. Low-temperature grinding prevents thermal degradation. Ideal for mixing, fine grinding, sample preparation, R&D, and small batch production.

Technical specifications

Working temperature	-40°C~20°C
Gas consumption	4-5 L/h (0-10 °C)
Compatible liquid nitrogen tank	30 L / 50 L

These specifications describe the series. Confirm the selected model, power supply and configuration before ordering.



The liquid nitrogen planetary ball mill is a ball mill in which the grinding jar is placed in a heat shield environment, and liquid nitrogen gas is continuously input into the environment. Liquid nitrogen can promptly absorb the heat generated by the high-speed rotation of the grinding ball, so that the grinding space inside the grinding jar always maintains a low-temperature environment. It is ideal and necessary equipment for mixing, fine grinding, small batch sample preparation, small batch production and new product development. Tianchuang planetary ball mill is an ideal laboratory powder grinding equipment for scientific research institutes, universities, and corporate laboratories due to its small size, full functions, low noise, high efficiency, and easy operation. The equipment is usually equipped with 4 grinding jars, which can obtain four different samples each time. Tianchuang planetary ball mill can also be equipped with a vacuum grinding jar for grinding samples in a vacuum atmosphere.

Liquid nitrogen planetary ball mills are widely used in geology, mining, metallurgy, electronics,

building materials, ceramics, chemical industry, light industry, medicine, environmental protection and other departments. Suitable for electronic ceramics, structural ceramics, magnetic materials, lithium cobalt oxide, lithium manganese acid, catalysts, phosphors, long afterglow luminescent powder, rare earth polishing powder, glass powder, fuel cells, zinc oxide varistors, piezoelectric ceramics, nanomaterials, capacitors, M LCC, thermistor (PTC, NTC), ZnO varistors, dielectric ceramics, alumina ceramics, zirconia ceramics, phosphor powder, zinc oxide powder, cobalt oxide powder, Ni-Zn ferrite, Mn-Zn ferrite and other production fields.

Technical parameters

Working temperature control range: -40°C~20°C

Gas consumption (0-10°C): 4-5 liters/hour

Machine size: 460×660×720mm

Machine net weight: about 80 kg

Compatible liquid nitrogen tanks: 30 liters/50 liters (see attached liquid nitrogen tank parameters)

Other parameters are the same as XQM- (2- 6) series

model	total volume	Voltage	power	Speed	net weight	net size
XQM-1C	1L	220V or 110V	0.75KW	70-670 rpm	83kgs	750*470*590mm
XQM-2C	2L	220V or 110V	0.75KW	70-670 rpm	85kgs	750*470*590mm
XQM-4C	4L	220V or 110V	0.75KW	70-670 rpm	88kgs	750*470*590mm
XQM-6C	6L	220V or 110V	0.75KW	70-670 rpm	93kgs	750*470*590mm
XQM-8C	8L	220V or 110V	1.5KW	70-580 rpm	150kgs	880*560*670mm
XQM-10C	10L	220V or 110V	1.5KW	70-580 rpm	150kgs	880*560*670mm
XQM-12C	12L	220V or 110V	1.5KW	70-580 rpm	150kgs	880*560*670mm

Contact

Changsha Tianchuang Powder Technology Co., Ltd. / Changsha, Hunan, China

Email: lichang0516@gmail.com

Phone / WhatsApp: +86 731 84027560 / WhatsApp +86 19021571516

<https://www.tencanballmills.com/en/products/grinding-series/planetary-ball-mill/liquid-nitrogen-planetary-ball-mill.html>

Before operation, review the selected model's instructions and the material requirements.